




Variable Pick Head

ML #306008

BENEFITS


- Seven vertical pneumatic actuators
- 12 mm bore, other bore sizes available
- 1" stroke, other stroke lengths available
- Fine stroke adjustments
- All vertical slides use ground rail technology
- Center cylinder doesn't move horizontally
- Other six cylinders move horizontally
- All cylinders move by three belt system on ground rails
- Easy installation
- Increased production and lower maintenance costs
- Speed and precision are dependent on motor, gear, and belt system
- Other configurations available



Extend View



Retract View



Customer supplied tooling is designed for confined spaces.

SPECIFICATIONS


Minimum Operating Pressure	20 psi
Operating Temperature	-20° to 80°F
Vertical Repeatability	+/- .001
Electric Motor:	Closed Loop step motor 24 VDC
Max Holding Torque:	8.88 lb-in

© Copyright 2008, by PHD, Inc. All Rights Reserved. Printed in the U.S.A.

CP306008




PHD is a member of the
MAC Distributor Network



PHD, Inc. • P.O. Box 9070 • Fort Wayne, IN 46899 • (260) 747-6151 • FAX (260) 747-6754
www.phdinc.com • phdinfo@phdinc.com

DIMENSIONS: VARIABLE PICK HEAD

ML#306008



CP306008

PHD, Inc.
 9009 Clubridge Drive
 P.O. Box 9070, Fort Wayne, Indiana 46899 U.S.A.
 Phone (260) 747-6151 • Fax (260) 747-6754
 www.phdinc.com • phdinfo@phdinc.com

PHDinEurope GmbH
 Arnold-Sommerfeld-Ring 2
 52499 Baesweiler, Germany
 Tel. +49 (0)2401 805 230 • Fax +49 (0)2401 805 232
 www.phdinc.com • info@PHDinEurope.de